P-TRAK[®] ULTRAFINE PARTICLE COUNTER MODEL 8525

The TSI's P-Trak® Ultrafine Particle Counter (UPC) 8525 is an ideal instrument for measuring workplace ultrafine particulate levels, as well as helping eliminate indoor air quality (IAQ) problems. This portable instrument detects and counts ultrafine particles (smaller than one micrometer) that often accompany or signal the presence of a pollutant that is the root cause of complaints.



Ultrafine particles are defined as having a diameter less than 0.1 µm (or 100 nm). Engineered nanoparticles (nanomaterials) are a subset of ultrafine particles with dimensions from 1 to 100 nm. Nanomaterials are produced and used for industrial and high-tech applications, while ultrafine particles are the byproducts of combustion and other chemical reactions. Unfortunately, the occupational health risks associated with manufacturing and using nanomaterials are not clearly understood. As a result, a need has arisen to assess workplace conditions. Using TSI's proven technology, the P-Trak gives direct, real-time measurement of workplace ultrafine particulate levels.

The P-Trak UPC also locates obvious pollutant sources such as boilers, furnaces, and vehicles, and it also detects the not-so-obvious sources such as photocopy machines and printers. Use this instrument to detect the migration of toxic exhaust gases, malfunctioning office equipment, pinhole gasket leaks in boilers and a wide variety of other problems.

Applications

- + Check office equipment
- + Clean room containment checks
- + Filter checks
- + Check fume hoods
- + Check safety cabinets
- + Vehicle emission migration
- + Combustion leaks
- + Control smoking areas

Features and Benefits

- + Real-time ultrafine particle counter
- + Solves tough IAQ problems
- + Easy to use
- + Data log information



UNDERSTANDING, ACCELERATED

SPECIFICATIONS

P-TRAK ULTRAFINE PARTICLE COUNTER MODELS 8525

32 to 100°F (0 to 38°C)

700 cm³/min (nominal)

100 cm³/min

6 AA alkaline

470

6 hrs at 70°F (21°C)

8 hours at 70°F (21°C)

100% reagent grade isopropyl

1,000 hours at one-minute intervals.

-40 to 160°F (-40 to 70°C)

Concentration Range 0 to 5×10^5 particles/cm³

Particle Size Range 0.02 to 1 micrometer

Temperature Range Operation Storage

Flow Rate Sample Total

Power Requirement

Battery type Battery life

Alcohol Requirement

Type Hours per charge

RS232 Output Baud rate 9600


Memory

Single points Data logging

A maximum of 141 separate tests.¹

Size (H x W x D)

10.75 in. x 5.5 in. x 5.5 in. (27 cm x 14 cm x 14 cm)



Easy-to-use TrakPro™ Data Analysis Software stores, organizes and reports test results.



UNDERSTANDING, ACCELERATED

TSI Incorporated - Visit our website www.tsi.com for more information.

USA	Tel: +1 800 874 2811	India	Tel: +91 80 67877200
UK	Tel: +44 149 4 459200	China	Tel: +86 10 8251 6588
France Germany	Tel: +33 4 91 11 87 64 Tel: +49 241 523030	Singapore	Tel: +65 6595 6388

Weight

Instrument with batteries Factory Recalibration Interval 3.8 lbs (1.7 kg) One year

Warranty

Two years on parts and labor²

Computer Requirements

PC with Microsoft Windows® 2000 or XP; Windows-compatible printer; 5 MB hard disk space; and available RS232 serial port (for downloading)



P-Trak Ultrafine Particle Counter and accessories includes: Telescoping Sample Probe, Shoulder Strap, Inlet Screen, Spare Wicks (2), Alkaline Batteries, Alcohol Fill Capsule with Storage Cap, Reagent Grade Isopropyl Alcohol, Zero Filters (2), Carrying Case, TrakPro^m Software, Computer Cable, Operation and Service Manual, Calibration Certificate, and Two-year Warranty.

 The P-Trak will operate with an AC adapter for long periods but the alcohol wick must be resaturated every 8 hours when operating over an extended time.
Warranty repairs returned via overnight carrier at TSI expense.

Specifications are subject to change without notice.

P-Trak, TSI and the TSI logo are registered trademarks, and TrakPro is a trademark of TSI Incorporated.

Microsoft and Windows are registered trademarks of Microsoft Corporation in the United States and/or other countries.

©2012 TSI Incorporated



We represent this supplier. For more information contact Observator Instruments:

T: +31 (0)180 463411 E: info@observator.com

Rietdekkerstraat 6 2984 BM Ridderkerk The Netherlands

Welcome to the world of Observator

Since 1924 Observator has evolved to be a trend-setting developer and supplier in a wide variety of industries. Originating from the Netherlands, Observator has grown into an internationally oriented company with a worldwide distribution network and offices

in Australia, Germany, the Netherlands, Singapore and the United Kingdom.

www.observator.com